

# Oxygen Mask






## High Concentration with standard connector

### Intended use:

High concentration masks are intended for administration of oxygen. They are equipped with a reservoir bag allowing an adequate amount of oxygen to be available to meet unpredictable breathing patterns and tidal volumes. Oxygen concentration delivered is 80%-100% depending on the patient's breathing rate and tidal volume. The product is intended for single use only.



### Product range:

	REF*	Item	Size	Description	Tube length
	9-104MM	High Concentration Oxygen Mask Rebreather	Adult	High Concentration Oxygen Mask, Rebreathing mask (elongated) with nose clip, No side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-104MMV (Vanilla scented mask)	High Concentration Oxygen Mask Rebreather	Adult	High Concentration Oxygen Mask, Rebreathing mask (elongated) with nose clip, No side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-224MM	High Concentration Oxygen Mask Rebreather	Pediatric	High Concentration Oxygen Mask, Rebreathing mask (elongated) with nose clip, No side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-224MMV (Vanilla scented mask)	High Concentration Oxygen Mask Rebreather	Pediatric	High Concentration Oxygen Mask, Rebreathing mask (elongated) with nose clip, No side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-264MM	High Concentration Oxygen Mask Rebreather	Infant	High Concentration Oxygen Mask, Rebreathing mask with nose clip, No side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-108MM	High Concentration Oxygen Mask Non-Rebreather	Adult	High Concentration Oxygen Mask, Non-rebreathing mask (elongated) with nose clip, 2 side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-108MMV (Vanilla scented mask)	High Concentration Oxygen Mask Non-Rebreather	Adult	High Concentration Oxygen Mask, Non-rebreathing mask (elongated) with nose clip, 2 side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-230MM	High Concentration Oxygen Mask Non-Rebreather	Pediatric	High Concentration Oxygen Mask, Non-rebreathing mask (elongated) with nose clip, 2 side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-230MMV (Vanilla scented mask)	High Concentration Oxygen Mask Non-Rebreather	Pediatric	High Concentration Oxygen Mask, Non-rebreathing mask (elongated) with nose clip, 2 side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')
	9-266MM	High Concentration Oxygen Mask Non-Rebreather	Infant	High Concentration Oxygen Mask, Non-rebreathing mask with nose clip, 2 side valves, 2.1m (7') No-crush oxygen tube, Standard connector	2.1m (7')

\* Products may not be available in all countries. Please contact your regional ConvaTec sales representative for further information.

### Material specifications:

**Contains latex?** . . . . . No  
**Contains phthalates?** . . . . . No  
**Contains bisphenols?** . . . . . No  
**Mask** . . . . . Polyvinyl chloride  
**Elastic strap** . . . . . Polyester  
**Nose clip** . . . . . Aluminum  
**Oxygen nipple connector** . . . . . High density polyethylene  
**Oxygen tube** . . . . . Polyvinyl chloride  
**Tube connector** . . . . . Polyvinyl chloride  
**Reservoir bag** . . . . . Polyvinyl chloride  
**Check valve** . . . . . Silicone  
**Side valves** . . . . . Silicone

### Certifications:

**CE-marking?** . . . . . Yes (CE 0120)  
**Product classification** . . . . . Class IIA (EU)  
**Quality system certified to** . . . . . EN ISO 13485:2012

### Sterilization:

**Sterile?** . . . . . No  
**Shelf life** . . . . . 5 years

# Oxygen Mask

High Concentration with standard connector



## Packaging specifications:

REF	Primary package	Secondary package/Polybag	Tertiary package/Shipper			Pallet
	Qty, pcs	Qty, pcs	Qty, pcs	Dimensions, mm (LxWxD)	Gross Wt., kg	Qty, pcs
9-104MM	1	10	50	400 x 380 x 260	4.27	900
9-104MMV	1	10	50	400 x 380 x 260	4.27	900
9-224MM	1	10	50	400 x 380 x 260	3.51	900
9-224MMV	1	10	50	400 x 380 x 260	3.51	900
9-264MM	1	10	50	400 x 380 x 260	3.30	1,600
9-108MM	1	10	50	400 x 380 x 260	4.27	900
9-108MMV	1	10	50	400 x 380 x 260	4.27	900
9-230MM	1	10	50	400 x 380 x 260	3.51	900
9-230MMV	1	10	50	400 x 380 x 260	3.51	900
9-266MM	1	10	50	400 x 300 x 240	3.30	1,600

## EAN codes:

REF	Primary package	Secondary package	Tertiary package
9-104MM	(01)06945099301581	(01)26945099301585	(01)46945099301589
9-104MMV	(01)06945099301796	(01)26945099301790	(01)46945099301794
9-224MM	(01)06945099301598	(01)26945099301592	(01)46945099301596
9-224MMV	(01)06945099301819	(01)26945099301813	(01)46945099301817
9-264MM	(01)06945099301833	(01)26945099301837	(01)46945099301831
9-108MM	(01)06945099301659	(01)26945099301653	(01)46945099301657
9-108MMV	(01)06945099301802	(01)26945099301806	(01)46945099301800
9-230MM	(01)06945099301604	(01)26945099301608	(01)46945099301602
9-230MMV	(01)06945099301826	(01)26945099301820	(01)46945099301824
9-266MM	(01)06945099301840	(01)26945099301844	(01)46945099301848

## Packaging material:

Primary package	Poly bag - Low density polyethylene / Insert - 80g paper
Secondary package	Poly bag - Low density polyethylene / Sticker - Coated paper
Tertiary package	Carton - Corrugated board / Sticker - Coated paper

## Storage and handling:

	<b>FRAGILE</b> - Contents of the transport package are fragile and shall therefore be handled with care
	<b>KEEP DRY</b>
	<b>THIS WAY UP</b> - Indicates correct upright position of the transport package
	<b>DO NOT USE HAND HOOKS</b> - Hooks are prohibited for handling the transport package



**Ningbo Shengyurui Medical Appliances Co., Ltd.**

No. 138 Binhaisi Rd.  
Hangzhou Bay New Zone, 315336, Ningbo City  
Zhejiang Province, P.R. China

Made in China



**Shanghai Intl. Holding Corp. GmbH**

Eiffestrasse 80, 20537 Hamburg  
Germany

Distributed by



ConvaTec Limited  
First Avenue, Deeside Industrial Park  
Deeside, Flintshire, CH5 2NU, UK

[www.convatec.com](http://www.convatec.com)

**For further information on these products, please contact your local ConvaTec sales representative.**

*With reservations for misprints and alterations in product specifications. Printed version not controlled.*

*All trade marks and logos are the property of a ConvaTec group company.*

© 2018 ConvaTec Inc. AP-018701-MM, ver. MAR 2018